

GLEICHSPANNUNGEN MIT GRUNDIG UNIVERSALVOLTMESSER UV 5A (Ri = 30 MΩ) GEGEN MASSE GEMESSEN.  
DC VOLTAGES MEASURED TO CHASSIS WITH GRUNDIG UNIVERSAL VVM UV 5A (Ri = 30 MΩ)


WECHSELSPANNUNGEN MIT GRUNDIG MILLIVOLTMESSER MV 50 GEMESSEN (f = 100 Hz, ~ 10 V)  
AC VOLTAGES MEASURED WITH GRUNDIG MILLIVOLTMESSER MV 50 (f = 100 Hz, ~ 10 V)

Z 0207

ELEKTROLYT  
ELECTROLYTIC

TRANSISTOR-ANSCHLÜSSE  
TRANSISTOR-CONNECTIONS

BC 548 B, BC 558 B




**Tongenerator  
TG 6**

(40205-942.01)

Blatt 2

**GRUNDIG  
electronic**



Z 0207

TRANSISTOR-ANSCHLÜSSE  
TRANSISTOR-CONNECTIONS



BC 548 B, BC 558 B  
BC 558 C

GLEICHSPANNUNGEN MIT GRUNDIG UNIVERSALVOLTMESSER UV 5A (Ri = 30 MΩ) GEGEN MASSE GEMESSEN.  
DC VOLTAGES MEASURED TO CHASSIS WITH GRUNDIG UNIVERSAL VVM UV 5A (Ri = 30 MΩ)

WECHSELSPANNUNGEN MIT GRUNDIG MILLIVOLTMESSER MV 50 GEMESSEN (f = 100 Hz, ~ 10 V)  
AC VOLTAGES MEASURED WITH GRUNDIG MILLIVOLTMESSER MV 50 (f = 100 Hz, ~ 10 V)

**Tongenerator  
TG 6**

(40205-942.01)

Blatt 3

**GRUNDIG  
electronic**